



ITEMS IN THE LID

- 1. 5mm and 4mm Allen Keys
- 2. **LEF75-THF/F** Flange End Fitting, female, 3/4" ball (indexing or articulating LiteMount)
- 3. **LEF75-JB** Jelly Bean End Fitting, 3/4" ball (indexing or articulating LiteMount)
- 4. EH87-AQR Elesa Handle for 7/8" Ball Joint (AFJ875) for use with AQR on Articulating LiteMount
- 5. **EH75-AQR** Elesa Handle for 3/4" Ball Joint (AFJ750) for use with AQR on Articulating LiteMount
- 6. EH75-AQR Elesa Handle for 3/4" Ball Joint (AFJ750) for use with AQR on Articulating LiteMount
- 7. BTS-6-04 5/8" diameter tube with 3/4" ball, 4"/100mm long, for use with Indexing LiteMount (final length)
- 8. **BTS-6-06** 5/8" diameter tube with 3/4" ball, 6"/150mm long, for use with Indexing LiteMount (final length)
- 9. **BTS-6-08** 5/8" diameter tube with 3/4" ball, 8"/200mm long, for use with Indexing LiteMount (final length)
- 10. LTS-6-04 5/8" diameter tube, 4"/100mm long, for use with Indexing Lite Mount (second length)
- 11. LTS-6-08 5/8" diameter tube, 8"/200mm long, for use with Indexing Lite Mount (second length)
- 12. LTS-6-12 5/8" diameter tube, 12"/300mm long, for use with Indexing Lite Mount (second length)
- 13. **LEF75-BB** Buddy Button End Fitting, 3/4" ball—underneath are 2 fixing screws (indexing or articulating LiteMount)
- 14. **SLV** Sleeves for LiteMount Frame Clamp, 1"-7/8", 1"-22mm
- 15. TCL-7-06 Telescoping Clamp to join a 3/4" diameter tube to a 5/8" diameter tube
- 16. **EH87-SW** Elesa Handle for 7/8" Ball Joint (AFJ875) for use with a switch end fitting on an Articulating LiteMount
- 17. EH75-AQR Elesa Handle for 3/4" Ball Joint (AFJ750) for use with a switch end fitting on an Articulating LiteMount
- 18. EH75-AQR Elesa Handle for 3/4" Ball Joint (AFJ750) for use with a switch end fitting on an Articulating LiteMount
- 19. LTS-7-08 3/4" diameter tube, 8"/205mm long, for use with Indexing Lite Mount (first length)
- 20. LTS-7-12 3/4" diameter tube, 12"/300mm long, for use with Indexing Lite Mount (first length)
- 21. LTS-7-16 3/4" diameter tube, 16"/410mm long, for use with Indexing Lite Mount (first length)

ITEMS IN THE BASE

- 22. **BTS-7-14** 3/4" diameter tube with 7/8" ball, 14"/355mm long, for use with Articulating LiteMount (first length)
- 23. **BTS-7-10** 3/4" diameter tube with 7/8" ball, 10"/255mm long, for use with Articulating LiteMount (first length)
- 24. **BTS-7-06** 3/4" diameter tube with 7/8" ball, 6"/150mm long, for use with Articulating LiteMount (first length)
- 25. **AFJ750** Ball Joint to take 2 x 3/4" balls (indexing or articulating LiteMount)
- 26. **AFJ750** Ball Joint to take 2 x 3/4" balls (indexing or articulating LiteMount)
- 27. ITC075-IN/ITC062 Hirth Clamp, for 3/4" dia tube, with insert and 5/8" dia tube, for use with indexing Lite Mount
- 28. ITC075/ITC062IN Hirth Clamp, for 3/4" dia tube and 5/8" dia tube, with insert, for use with indexing Lite Mount
- 29. ITC062-IN/ITC062 Hirth Clamp, for 2 x 5/8" tube, for use with indexing Lite Mount
- 30. **BT2-6-08** 5/8" dia tube with 7/8" ball and 3/4" ball, 8"/200mm long, for use with Articulating LiteMount (second length)
- 31. **BT2-6-06** 5/8" dia tube with 7/8" ball and 3/4" ball, 6"/150mm long, for use with Articulating LiteMount (second length)
- 32. **BT2-6-04** 5/8" dia tube with 7/8" ball and 3/4" ball, 4"/100mm long, for use with Articulating LiteMount (second
- 33. **LMO3L** LiteMount Offset Link to connect a LiteMount clamp assembly to a standard Daessy frame clamp inner
- 34. **LIPA** LiteMount Inner Piece Adaptor to connect a LiteMount clamp assembly to any standard Daessy frame clamp with an IPA (replaces standard IPA)
- 35. M6-16 2 x 16mm M6 bolt for use with LIPA
- 36. **M6-40** 2 x 40mm M6 bolt for use with ITC062-IN/ITC062
- 37. M6-50 2 x 50mm M6 bolt for use with ITC075-IN/ITC062 or ITC075/ITC062-IN
- 38. **ILMCQ/01** Lite Mount Clamp Assembly including 1" round clamp inner (ITC010-IN), LiteMount Frame Clamp Outer Connector (LMCQ/R) and LiteMount Frame Clamp Insert (LMCQ/I)
- 39. **LEF-75/AQR** Lite Mount Articulating Quick Release Base
- 40. Tape Measure
- 41. **AFJ875** Ball Joint to take 2 x 7/8" balls, for use witharticulating LiteMount
- 42. **BTT-6-06** 5/8" dia tube with 2 x 3/4" ball, 6"/150mm long, for use with Articulating LiteMount (third length)
- 43. **BTT-6-04** 5/8" dia tube with 2 x 3/4" ball, 4"/100mm long, for use with Articulating LiteMount (third length)
- 44. **BTT-6-02** 5/8" dia tube with 2 x 3/4" ball, 2"/50mm long, for use with Articulating LiteMount (third length)
- 45. Pen